

SEL-401

Protection, Automation, Control Merging Unit with IEC 61850-9-2LE Sampled Values, Phase Overcurrent, and Breaker Failure Protection

Part Number: **0 4 0 1 0 X 3 0 0 X D X X**

Firmware

Standard

Connector Type

Screw Terminal
 Connectorized® Relay*

Secondary Current Inputs

1 Amp
 5 Amp

Secondary Voltage Inputs and Conformal Coat

300V Phase Neutral with Conformally Coated Circuit Boards

Power Supply

48 - 125 Vdc or 110 - 120 Vac
 125 - 250 Vdc or 110 - 240 Vac

Ethernet Communications Protocols⁽¹⁾

FTP, Telnet, Synchrophasors, DNP3, IEC 61850, and IEC 61850-9-2LE Publish

Ethernet Connection Options⁽²⁾

Four 10/100BASE-T Connectors
 Four 100BASE-FX Connectors*
 Two 10/100BASE-T and Two 100BASE-FX Connectors^{(3)*}

Mounting

Horizontal Rack Mount
 Horizontal Panel Mount
 Vertical Rack Mount
 Vertical Panel Mount

Chassis

4U, One I/O Board
 5U, Up to Two I/O Boards
 6U, Up to Three I/O Boards

I/O Board Position B for 4U, 5U, 6U Chassis

8 Optoisolated Independent Level-Sensitive Inputs, 13 Standard Form A, 2 Standard Form C Outputs*
 8 Optoisolated Independent Level-Sensitive Inputs, 13 High-Current Interrupting Form A, 2 Standard Form C Outputs*

