

**SEL-3373**

Station PDC

Part Number:

3	3	7	3	2			1			2	0						X	X	X	X
---	---	---	---	---	--	--	---	--	--	---	---	--	--	--	--	--	---	---	---	---

**Processor**

Standard						2																				
----------	--	--	--	--	--	---	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--

**Power Supply**

48/125 Vdc or 120 Vac							M																			
-----------------------	--	--	--	--	--	--	---	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--

125/250 Vdc or 120/240 Vac							H																			
----------------------------	--	--	--	--	--	--	---	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--

**Serial Ports**

16 Ports								1																		
----------	--	--	--	--	--	--	--	---	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--

**Rear Ethernet Ports**

Dual Copper 10/100BASE-T											0															
--------------------------	--	--	--	--	--	--	--	--	--	--	---	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--

Dual Fiber 100BASE-FX *											2															
-------------------------	--	--	--	--	--	--	--	--	--	--	---	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--

**Compact Flash Storage**

8 GB											2	0														
------	--	--	--	--	--	--	--	--	--	--	---	---	--	--	--	--	--	--	--	--	--	--	--	--	--	--

**Solid-State Drive (SSD) Storage**

None														0												
------	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--	--	--	--	--	--	--	--	--	--	--	--

60 GB Solid State Drive (SSD) Storage <sup>(1)*</sup>														1												
---	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--	--	--	--	--	--	--	--	--	--	--	--

120 GB Solid State Drive (SSD) Storage <sup>(1)*</sup>														2												
--	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--	--	--	--	--	--	--	--	--	--	--	--

**Mounting**

Horizontal Rack Mount																H	X									
-----------------------	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	---	---	--	--	--	--	--	--	--	--	--

Horizontal Panel Mount															3	X										
------------------------	--	--	--	--	--	--	--	--	--	--	--	--	--	--	---	---	--	--	--	--	--	--	--	--	--	--

**Performance Options**

Base Product (includes up to 8 PMU inputs)																								0			
--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--	--	--

Base Plus Archiving Capability <sup>(1)*</sup>																								1			
--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--	--	--

Base Plus Ability To Connect The Maximum Number of PMUs (Up To 40 PMUs)*																									2			
--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--	--	--

Base Plus Archiving Capability and Ability To Connect The Maximum Number of PMUs (Up To 40 PMUs) <sup>(1)*</sup>																									3			
--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--	--	--

\* Additional Cost

<sup>(1)</sup> 60GB or 120 GB SSD drive is required to add Archiving Capability. Archiving Capability is also required to add an SSD drive.

Note: The SEL-3373 comes standard with a CD manual. A printed instruction manual is available upon request.

Note: The SEL-3373 ships with the PDC Assistant software. The PDC Assistant software can be loaded on your Windows based computers, and is used to set up and view real-time status of the SEL-3373.

*Making Electric Power Safer, More Reliable, and More Economical<sup>®</sup>*