

Accessories

Allen Bradley 193-CBCT1, 1000:1 Turns Ratio, 45 A Max Current, 0.75" Diameter Window*	9 1 5 9 0 0 2 7 0
Allen Bradley 193-CBCT2, 1000:1 Turns Ratio, 90 A Max Current, 1.56" Diameter Window*	9 1 5 9 0 0 2 8 5
Allen Bradley 193-CBCT3, 1000:1 Ratio, 180 A Max, 2.50" Diameter. Use when the grounding resistor is on the NGT secondary.*	9 1 5 9 0 0 2 8 6
SEL-3421 Motor Relay HMI w/LCD*	Please see Online MOT or contact SEL REP or CSR for ordering information.
SEL-3422 Motor Relay HMI*	Please see Online MOT or contact SEL REP or CSR for ordering information.
SEL-849 Accessory Lug Kit*	9 1 5 9 0 0 3 2 5
Configurable Label Kit - SEL-3421/SEL-3422*	9 1 5 9 0 0 2 6 8
Replacement Parts for SEL-3421/SEL-3422 - Mounting Screws, DIN Rail Clips and Supports (includes parts for up to 5 HMIs)*	9 1 5 9 0 0 2 6 9
Replacement Set of SEL-849 Europlug Connectors*	9 1 5 9 0 0 2 7 4
MCC Rated Category 5e Ethernet Cable - Double-Shielded, 600V (configurable length)	C 6 2 7 M
Standard Category 5e Ethernet Cable (configurable length)	C 6 2 7
DTE Device to SEL-849 Serial Cable, EIA-232 (configurable length)	C 2 3 4 T
SEL Communications Processor to SEL-849 Serial Cable, EIA-232 (configurable length)	C 2 8 5 T
Literature	
SEL-849 Instruction Manual	P M 8 4 9 - 0 1
SEL-849 Instruction Manual - CD Only	P M 8 4 9 - 0 1 - C D
SEL-849 Instruction Manual - Printed, No Binder	P M 8 4 9 - 0 1 - N B

Making Electric Power Safer, More Reliable, and More Economical®

SEL SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA
Phone: +1.509.332.1890 - Fax: +1.509.332.7990