

SEL-2020

Communications Processor



**SCHWEITZER
ENGINEERING
LABORATORIES**

2350 NE Hopkins Court • Pullman, WA 99163-5603 USA
Phone: (509) 332-1890 • Fax: (509) 332-7990
Internet: www.selinc.com • E-mail: info@selinc.com

Ordering Information

Part Number Example: 20203121XH

Choose from the following options.
Enter option codes to complete the part number.

2 0 2 0

--	--	--	--	--	--

Option Codes

Memory

Standard (512K RAM, 32K EEPROM)		0					
Expanded Database and Settings Storage (1 MB RAM, 64K EEPROM)	*	1					
Expanded Database and Settings Storage, plus Archive Storage Memory (1 MB RAM, 64K EEPROM, 2 MB Flash)	*	3					

Telephone Modem

None		0					
33,600 BPS, Internal	*	1					

Power Supply; Control Input Voltage⁽¹⁾

20-60 Vdc	48 Vdc			2			
38-200 Vdc, 85-140 Vac	48 Vdc			3			
38-200 Vdc, 85-140 Vac	125 Vdc			A			
85-350 Vdc, 85-264 Vac	125 Vdc			4			

I/O Board

No I/O Board				0			
4 Outputs, 16 Inputs	*			1			

Mounting

Horizontal Rack Mount					X	H
Horizontal Panel Mount					X	3
Horizontal Projection Panel Mount	*				X	5

* Additional Cost

⁽¹⁾ If I/O board is ordered, Control Input Voltage is jumper-selectable (48, 125, 250 Vdc).

Note: The SEL-2020 comes standard with a CD manual. A printed instruction manual is available upon request.