

Instructions for Creating Part Numbers

Please consult with your SEL representative on available displays and other configuration options before ordering.

1. Select one code (in bold) from each column. List option codes in the order that they appear in the column.
2. Follow your usual process to issue a purchase order, or complete a specification for standards.

SEL-TPR Underground Test Point Reset Fault Indicator									
Phase	BEACON® LED Option	SEL-TPR Designation	Display	Nominal Trip Rating	Inrush Restraint	Options			
1	– No BEACON	TPR	I Integral*	0060 60 A	IR	–	No Options		
3	B BEACON LED		V Standard Remote	0080 80 A		A	Battery-Powered Auxiliary Contact**		
			L Large Remote	0100 100 A		DT	Delayed Trip (24 ms)		
			B Bolt	0160 160 A		J	200 A-Class Junction Shields [†]		
			M Magnetic Probe (RadioRANGER® required)	0200 200 A			600 A-Class Junction Shields [†]		
				0250 250 A		J6	Window-Mounting Kit for Large Remote Display		
				0300 300 A		W			
				0400 400 A					
				0450 450 A					
				0600 600 A					
				0800 800 A					
				1000 1,000 A					
			1200 1,200 A						

*Only available with single-phase SEL-TPR.

**Not available with "I" display.

[†]Required ≤200 A trip ratings. Suggested for junction enclosure applications or when phase distinction is required.

[‡]Required on 600 A-class elbows when applied to junction applications.

Please consult with your SEL representative on available displays and other configuration options before ordering.

Example part number: 3BTPRV0200IRDT

This example part number is for a three-phase SEL-TPR with a BEACON LED, standard remote display, 200 A nominal trip rating, inrush restraint, and delayed trip.

SEL-TPR for Basic Insulating Plug (BIP)									
Phase	Voltage Reset SEL-TPR Designation	Display	Nominal Trip Rating	Inrush Restraint	Options	Delayed Trip	Core Mounting Diameter Range	kV Class	
3	VRP Voltage Reset for BIP	V Standard Remote	1200 1,200 A 1500 1,500 A	IR	– No Options A Auxiliary Contact	DT Delayed Trip (24 ms)	– Standard Core (0.75"– 2.1") L Large Core (1.8"–2.5")	9 35 kV	

Example Part Number: 3VRPV1200IRDTL9

This example part number is for a three-phase SEL-TPR with voltage reset for a BIP, standard remote display, 1,200 A nominal trip rating, inrush restraint, delayed trip, large core, and 35 kV class.



Making Electric Power Safer, More Reliable, and More Economical
Tel: +1.509.332.1890 | Email: info@selinc.com | Web: www.selinc.com