

SEL-587-0, -1 Connectorized®

Current Differential Relay, Standard With 5 High Current Interrupting Outputs, 2 Inputs, Plug-In Connectors, and ACSELERATOR QuickSet® SEL-5030 Software⁽¹⁾

Part Number:

0	5	8	7																
---	---	---	---	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--

Firmware

Standard								0						X					
Standard plus Harmonic Restraint, Trip Unlatch, and Zero-Sequence Removal								1											

Connection Type; Conformal Coat

Connectorized; No Conformal Coat														W					
Connectorized; Conformal Coated Circuit Boards*														S					

Power Supply

24 Vdc														1					
48/125 Vdc or 125 Vac														3					
125/250 Vdc or Vac														6					

Communications Protocol

Standard														X					
Standard plus Modbus® (available only in 587-1)														2					

Secondary Input Current

1 A Phase																			1
5 A Phase																			5

Packaging

Horizontal Rack Mount																			X
Part of Two-Relay Rack Mount Package																			P
Single Relay Assembled With Rack Mount Bracket 9100 (bracket on right side in front view)																			B
Single Relay With Rack Mount Bracket 9102 w/Cutout for Test Switch (bracket on right side in front view)																			C
Horizontal Panel Mount																			3
Horizontal Projection Panel Mount*																			5

Communications Port⁽²⁾

EIA-232																			1
EIA-485*																			2

Control Input Voltage

24 Vdc																			1
48 Vdc (level sensitive inputs)																			2
110 Vdc (level sensitive inputs)																			3
125 Vdc (level sensitive inputs)																			4
250 Vdc (level sensitive inputs)																			6

Accessories

Literature		
	SEL-587-0, -1 Printed English Instruction Manual ⁽³⁾	P M 5 8 7 - 0 1
	SEL-587-0,-1 Printed Spanish Instruction Manual ⁽³⁾	P M 5 8 7 - 0 2
Wiring Harness		
	Connectorized [®] Wiring Harness for SEL-587 Relays ^{(4)*}	Please see Online MOT or contact SEL REP or CSR for ordering information.

* Additional Cost

⁽¹⁾ Download acSELERATOR QuickSet SEL-5030 software for free at <https://www.selinc.com/softwareolutions/>. QuickSet on CD (503001WX4) is available upon request.

⁽²⁾ Warning - EIA-485 is for special applications only. SEL strongly recommends ordering an EIA-232 port. If an EIA-485 port is ordered, SEL strongly recommends cable C671A to allow relay programming and event retrieval. All SEL-587 relays ordered with an EIA-485 port are shipped with a C675 Terminal Adapter to adapt from the on board DB-9 connector to an 8-pin screw terminal.

⁽³⁾ The SEL-587-0, -1 Connectorized[®] comes standard with a CD manual. One complimentary printed instruction manual is available upon request with each product purchased.

⁽⁴⁾ Order a Connectorized[®] Wiring Harness for SEL-587 (harness shipped separately).

Making Electric Power Safer, More Reliable, and More Economical[®]

SEL SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA
Phone: +1.509.332.1890 - Fax: +1.509.332.7990