

SEL-3031 Serial Radio Transceiver

Standard With 3 Serial Ports, ACSELERATOR QuickSet® SEL-5030 Software⁽¹⁾

Countries

The SEL-3031 is approved for use in the following countries:

- Brazil
- Canada
- Colombia
- Mexico
- United States (including the District of Columbia, Puerto Rico, Guam, American Samoa, and the American Virgin Islands)

Part Number:

3	0	3	1									X	X
---	---	---	---	--	--	--	--	--	--	--	--	---	---

Frequency

900 MHz Frequency Hopping, Spread Spectrum	0				
900 MHz FHSS, Brazil	1				

Mounting

Wall Mount	W	0			
Below-Shelf Mount (inverted front labeling)	B	0			
19 in Rack Mount*	R				
Nema 3R Outdoor Enclosure*	N	3			

Power Supply

9-30 Vdc, Wall Mount or Below-Shelf Mount only	0				
24/48 Vdc	R	2			
48 Vdc/125 Vdc or Vac	N	3			
125/250 Vdc or Vac	R	4			

Port 1 Communication Option

EIA-232	1				
EIA-485	2				
SEL-2812R Compatible (ST® 850nm multimode fiber)*	3				

Encryption

None	X				
Encryption Card*	3				

Accessories

Feed Line ⁽²⁾		
	RG-8X TNC Male to N Male Cable	C 9 6 4
	LMR-400 TNC Male to N Male Cable	C 9 6 6
	LMR-400 N Male to N Male Cable	C 9 6 8
	Hop-Sync ^(TM) cable*	C 5 7 6
Antenna		
	3-Element, 8.15 dBi Yagi, N Female Connector*	2 3 5 - 0 0 0 9

	5-Element 11.1 dBi Gain Yagi, N Female Connector*	2 3 5 - 0 2 2 0
	11-Element 14.15 dBi Gain Yagi, N Female Connector*	2 3 5 - 0 2 2 2
	Low-Profile 3 dBi Gain Omnidirectional Antenna, N Female Connector*	2 3 5 - 0 0 0 3
	Vertical 7.15 dBi Gain Omnidirectional, N Female Connector*	2 3 5 - 0 2 3 2
	Vertical 9.15 dBi Gain Omnidirectional, N Female Connector*	2 3 5 - 0 2 3 3
	Indoor 8" Vertical TNC Connector*	2 3 5 - 0 1 0 8
Surge Protection		
	Radio Surge Protector With N Connectors*	2 0 0 - 2 0 0 4
	In-Line Grounding Cable (fits LMR-400 coaxial cable)*	2 4 0 - 0 1 2 4
Antenna Mount		
	Vertical Omnidirectional Antenna Mount for 14" Maximum Diameter Pole*	2 4 0 - 0 1 0 3
	Yagi Antenna Mount for 14" Maximum Diameter Pole*	2 4 0 - 0 1 0 4
	Omnidirectional Antenna Mount (2.5 in Max OD Antenna to 2.5 in Max OD Mast)*	2 4 0 - 0 1 0 6
	Mounting Bracket for Low-Profile Omnidirectional Antenna*	9 1 5 9 0 0 4 9 4
Field Upgrade Kits		
	Mounting Kit for SEL-351R ^{(3)*}	9 1 5 9 0 0 1 9 5
	Mounting Kit for Dual Door SEL-651R ^{(3)*}	9 1 5 9 0 0 1 8 1
	Mounting Kit for Single Door SEL-651R ^{(3)*}	9 1 5 9 0 0 1 8 0
	SEL-3044 Encryption Card*	9 1 5 9 0 0 1 7 2

* Additional Cost

⁽¹⁾ ACSELEATOR QuickSet[®] SEL-5030 Software (503001WX4) is provided with all SEL-3031 orders free of charge. For separate software orders, download QuickSet[®] SEL-5030 software for free at <https://www.selinc.com/software/solutions/>. QuickSet[®] on CD (503001WX4) is available upon request.

⁽²⁾ Required: please specify the cable length needed.

⁽³⁾ The Wall Mount version of the SEL-3031 must be specified for use with the SEL-351R and SEL-651R.

NOTE: The SEL-3031 comes standard with a CD manual. One complimentary printed instruction manual is available upon request with each product purchased.

Making Electric Power Safer, More Reliable, and More Economical[®]

SEL SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA
 Phone: +1.509.332.1890 - Fax: +1.509.332.7990