

SEL-C239 EIA-232 Serial Cable with IRIG-B

Split cable for connecting an SEL communication processor to an SEL-200 Series or SEL-321 Relay⁽¹⁾⁽²⁾

Part Number:

C 2 3 9 -


Length⁽³⁾

Specify in Feet with Leading Zeros (Example: 5 Feet = 005) Max length 100 Feet

⁽¹⁾ To verify your cable application, use the Cable Selector at <https://www.selinc.com/CableSelector/>.

⁽²⁾ Indoor Use Only, CM-Rated

⁽³⁾ The performance of EIA-232 cable lengths greater than 50 feet cannot be guaranteed. As cable lengths increase, so does the risk of interference and equipment damage due to ground potential rise and induced voltages. For lengths longer than 50 feet, we recommend the fiber-optic C239FZ/FD cable.



CABLE: 9 Conductor 22 AWG 7/30 Tinned Copper with PVC Jacket (Shielded: Alpha 1298C or equal)

SEL-2020/2030 (DTE)			SEL-Relay (DTE)		
RXD	2	ORANGE	3	TXD	
TXD	3	RED	2	RXD	
GND	5	YELLOW	5	GND	
RTS	7	GREEN	8	CTS	
CTS	8	WHITE	7	RTS	
SHELL		SHIELD		NO CONNECTION	

SEL-Relay IRIG Input		
+IRIGB	4	BLUE
-IRIGB	6	BLACK

Comments:

Making Electric Power Safer, More Reliable, and More Economical®