

SEL-2812H

EIA-232 Multimode Fiber-Optic Transceiver with IRIG-B Transmitter or Receiver. Meets or Surpasses Electric Utility Type Tests and Hardened for EHV Applications, up to 115.2 Kbps, 4 Kilometers.

Part Number:

2	8	1	2	H	M	
---	---	---	---	---	---	--

EIA-232 Connector

Male DB-9

						M
--	--	--	--	--	--	---

IRIG-B

IRIG-B Transmitter

						T
--	--	--	--	--	--	---

IRIG-B Receiver

						R
--	--	--	--	--	--	---

A complete installation of 2812H Transceivers requires:

- One SEL-2812HMT
- One SEL-2812HMR
- The appropriate length of Fiber-Optic cable with ST[®] Connectors.

SEL Multimode Fiber-Optic cable choices:

- Use SEL-C805 Multimode 200 μm cables and patchcords with ST Connectors (WI-4092)
- Use SEL-C807 Multimode 62.5/200 μm cables with ST Connectors (WI-4132)
- Use SEL-C808 Multimode 50/125 mm cables with ST Connectors (WI-9126)

IRIG-B Cables:

- C654 - 2812 J1 Mono Plug to BNC connector, 1.82 m (6 ft)
- C655 - 2812 J1 Mono Plug to DB-9 connector, 1.82 m (6 ft)
- C656 - 2812 J1 Mono Plug to Ring Terminals, 1.82 m (6 ft)

Use the SEL-5801 Cable Selector Program for a complete list of cables available from SEL.

Making Electric Power Safer, More Reliable, and More Economical[®]

SEL SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA
 Phone: +1.509.332.1890 - Fax: +1.509.332.7990