

SEL-C246A EIA-232 Serial Cable

Cable for connecting an SEL Communication Processor to a DCE device with a 9-Pin female connector⁽¹⁾⁽²⁾

Part Number:

C 2 4 6 A -

Length⁽³⁾

Specify in Feet with Leading Zeros (Example: 5 Feet = 005) Max length 100 Feet

⁽¹⁾ To verify your cable application, use the Cable Selector <https://www.selinc.com/CableSelector/>.

⁽²⁾ Indoor Use Only, CM-Rated

⁽³⁾ The performance of EIA-232 cable lengths greater than 50 feet cannot be guaranteed. As cable lengths increase, so does the risk of interference and equipment damage due to ground potential rise and induced voltages. For lengths longer than 50 feet, we recommend the fiber-optic C246AFZ/FD cable.



CABLE: 9 Conductor 22 AWG 7/30 Tinned Copper with PVC Jacket
(Shielded: Alpha 1298C or equal)

RXD	2	ORANGE	2	RXD (OUT)
TXD	3	RED	3	TXD (IN)
GND	5	SHIELD	5	GND
RTS	7		4	DTR (IN)
CTS	8		7	RTS (IN)
			8	CTS (OUT)

Making Electric Power Safer, More Reliable, and More Economical ®

SEL SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA
Phone: +1.509.332.1890 - Fax: +1.509.332.7990