

SEL-C940

DB-9 Female to dual BNC male connectors

Cable with a DB-9 Female connector (for SEL-3405) to dual BNC male connectors for IRIG-B and power when connecting to an SEL-3400

Part Number:

C 9 4 0 -

Length

Specify in Feet with Leading Zeros (Example: 5 Feet = 005) - Max Length 12 Feet

(1) To verify your cable application, use the cable selector at <https://www.selinc.com/CableSelector/>.



CABLE: 8 Conductor 22 AWG 7/30 Tinned Copper with PVC Jacket

SEL-3405			IRIG-B	
+IRIG B	4	ORANGE	CENTER	
IRIG B RTN	6	RED	SHIELD	
SHELL		SHIELD	NO CONNECTION	
			SEL-3400 Port 1 or 2	
+5 VDC INPUT	1	BLACK	CENTER	
	5	BLUE	SHIELD	

Comments: To enable +5V on OUT_1 and OUT_2 of the SEL-3400, turn on Control Switch 16 on the SEL-3400

Making Electric Power Safer, More Reliable, and More Economical®

SEL SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA
 Phone: +1.509.332.1890 - Fax: +1.509.332.7990