

## SEL-C227A

Cable for connecting a DTE device with a 9-pin female connector to a terminal with a 25-pin male connector.<sup>(1)(2)</sup>

Part Number:

**C 2 2 7 A -**

### Length<sup>(3)</sup>


Specify in feet with leading zeros (Example: 5 Feet = 005) Max length 100 Feet\*

\* Additional Cost

<sup>(1)</sup> To verify your cable application, use the Cable Selector at <https://www.selinc.com/CableSelector/>.

<sup>(2)</sup> Indoor Use only, CM-Rated

<sup>(3)</sup> The performance of EIA-232 cable lengths greater than 50 feet cannot be guaranteed. As cable lengths increase, so does the risk of interference and equipment damage due to ground potential rise and induced voltages.



9-PIN MALE  
"D" SUB CONNECTOR  
DB-9-P

25-PIN FEMALE  
"D" SUB CONNECTOR  
DB-25-S

LINE	5	BLACK	7	GND
TXD	3	RED	3	RXD
RXD	2	ORANGE	2	TXD
GND	9	YELLOW	1	GND
CTS	8	WHITE	4	RTS
			5	CTS
			6	DSR
			8	DCD
			20	DTR

*Making Electric Power Safer, More Reliable, and More Economical®*

**SEL** SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA  
Phone: +1.509.332.1890 - Fax: +1.509.332.7990