

## SEL-C323 EIA-232 Serial Cable with IRIG

Cable with PVC jacket<sup>(1)</sup> and standard shielding for connecting a DTE device to another DTE device with 9-pin female connectors<sup>(2)</sup>

Part Number:

**C 3 2 3 -**

### Length<sup>(3)</sup>

Specify in feet with leading zeros (Example: 5 Feet = 005) Max length 100 Feet

\* Additional Cost

<sup>(1)</sup> Indoor Use Only, CM-Rated

<sup>(2)</sup> To verify your cable application, use the Cable Selector at <https://www.selinc.com/CableSelector/>.

<sup>(3)</sup> The performance of EIA-232 cable lengths greater than 50 feet cannot be guaranteed. As cable lengths increase, so does the risk of interference and equipment damage due to ground potential rise and induced voltages. For lengths longer than 50 feet, we recommend the fiber-optic C273AFZ/FD cable.



**CABLE:** 8 Conductor 22 AWG 7/30 Tinned Copper with PVC Jacket

RXD	2	ORANGE	3	TXD
TXD	3	RED	2	RXD
+IRIG	4	BLUE	4	+IRIG
GND	5	BLACK	5	GND
-IRIG	6	YELLOW	6	-IRIG
RTS	7	GREEN	8	CTS
CTS	8	WHITE	7	RTS
SHELL		SHIELD		SHELL

**Making Electric Power Safer, More Reliable, and More Economical®**

**SEL** SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA  
 Phone: +1.509.332.1890 - Fax: +1.509.332.7990