

Socket Adapters		
	Socket Adapter Form 5*	9 1 5 9 0 0 2 5 6
	Socket Adapter Form 9*	9 1 5 9 0 0 2 5 7
	Form 5 EXM Test-Socket Adapter*	9 1 5 9 0 0 2 5 8
	Form 9 EXM Test-Socket Adapter*	9 1 5 9 0 0 2 5 9
Rack Mount Brackets		
	Single Horizontal Meter Bracket*	9 1 5 9 0 0 0 0 7
	Two Horizontal Meter Bracket*	9 1 5 9 0 0 0 0 8
	Horizontal Meter and FT-1 Test Switch Bracket*	9 1 5 9 0 0 0 0 9
	Meter and Two FT-1 Test Switch Bracket*	9 1 5 9 0 0 0 3 5
	Single Vertical Meter Bracket*	9 1 5 9 0 0 0 5 0
	Two Vertical Meter Bracket*	9 1 5 9 0 0 0 5 1
	Three Vertical Meter Bracket*	9 1 5 9 0 0 2 4 3
	Vertical Meter and two FT-1 Test Switch Bracket*	9 1 5 9 0 0 1 5 8
	Rack Mount Kit, 7xx/24xx Vertical and 7xx/24xx Horizontal Retrofit*	9 1 5 9 0 0 1 4 1
	Rack Mount Kit, 7xx/24xx Vertical*	9 1 5 9 0 0 1 6 9
	19" Rack Mount Bezel for 7xx/24xx Vertical (centered)*	9 1 5 9 0 0 2 2 8
	Vertical Meter and FT-1 Test Switch Bracket*	9 1 5 9 0 0 0 5 2
Wall Mount Brackets		
	Low-Profile Hinged Wall-Mount Bracket*	9 1 5 9 0 0 2 5 5
	Low-Profile, Hinged, Contains CT/PT Wiring and 1 Serial Cable*	9 1 5 9 0 0 3 1 7
	Low-Profile, Hinged, Contains CT/PT Wiring and 2 Serial Cables*	9 1 5 9 0 0 3 1 8
	Low-Profile, Hinged, Contains CT/PT Wiring and 3 Serial Cables*	9 1 5 9 0 0 3 1 9
	Vertical Hinged Wall-Mount Bracket*	9 1 5 9 0 0 1 3 6
	Horizontal Surface Mount Kit*	9 1 5 9 0 0 1 1 6

	7xx Wall-Mount Bracket*	9 1 5 9 0 0 0 4 7
	7xx Hinged Wall-Mount Bracket*	9 1 5 9 0 0 0 6 3
Retrofit Bezels		
	Vertical Retrofit (Schlumberger Q1000 SB) Bezel*	9 1 5 9 0 0 0 7 5
	Horizontal Meter and FT-1 Test Switch (Short SB) Retrofit Bezel*	9 1 5 9 0 0 0 0 5
	Single Horizontal Meter (Short SB) Retrofit Bezel*	9 1 5 9 0 0 0 0 6
	Horizontal Meter and FT-1 Test Switch (Tall SB) Retrofit Bezel*	9 1 5 9 0 0 0 2 3
	Single Horizontal Meter (Tall SB) Retrofit Bezel*	9 1 5 9 0 0 0 2 4
	Single Vertical Meter Retrofit Bezel*	9 1 5 9 0 0 0 5 3
	Vertical Appearance Bezel*	9 1 5 9 0 0 0 5 8
	Vertical Retrofit (JEM 1 SB) Bezel*	9 1 5 9 0 0 0 6 9
	Vertical Retrofit (JEM 1 Panel Mount) Bezel*	9 1 5 9 0 0 0 7 0
	Vertical Retrofit (GE kV) Bezel*	9 1 5 9 0 0 0 7 1
	Vertical Retrofit (JEMStar SB/TransData MK-5 SB) Bezel*	9 1 5 9 0 0 0 7 2
	Vertical Retrofit (Nexus 1260/1270 SB) Bezel*	9 1 5 9 0 0 0 7 3
	Vertical Retrofit (PML ION 8000 SB) Bezel*	9 1 5 9 0 0 0 7 4
	Vertical Retrofit (Siemens Q4 Tall SB) Bezel*	9 1 5 9 0 0 0 7 6
	Vertical Retrofit (Siemens Q4 Short SB) Bezel*	9 1 5 9 0 0 0 7 7
	Vertical Retrofit (GE 169/269/369 and Eaton FP5000)*	9 1 5 9 0 0 0 5 4
	Vertical Retrofit (GE 469)*	9 1 5 9 0 0 0 5 5
	Vertical Retrofit (Cutler-Hammer MP-3000)*	9 1 5 9 0 0 0 5 7
	ABB FT-21/22 (CO FT-2) to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 0 7 8
	GE F650 to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 0 7 9

GE 700 Series to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 0 8 0
Basler 851/951 to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 0 8 1
ABB 500 Series to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 0 8 2
Siemens 7SJ61 (1/3 rack case) to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 0 8 3
ABB 500 Series (1/2 rack case) to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 0 8 6
GE ML 269 Plus With Drawout Case Option to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 0 9 9
ABB-FT 31/32 (CO FT-3) to 7xx/24xx Vertical Retrofit with 2 FT-1 Switch Cutouts*	9 1 5 9 0 0 1 3 0
GE MDP/S2 to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 1 3 2
GE M1 to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 1 3 3
GE M2 to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 1 3 4
GE 565 to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 1 4 5
ABB-FT 41/42 (CO FT-4) to 7xx/24xx Vertical Retrofit with 2 FT-1 Switch Cutouts*	9 1 5 9 0 0 1 5 6
ABB DPU to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 1 5 7
GE S1 (IAC S1) to 2 FT-1 Switch Cutouts*	9 1 5 9 0 0 1 5 9
GE 269/369 to 7xx/24xx Vertical Retrofit with FT-1 Switch Cutout*	9 1 5 9 0 0 1 6 5
EXM Retrofit Bezel, JEMStar SB/TransData MK-5 SB*	9 1 5 9 0 0 1 9 6
PML 37xx to 7xx Horizontal Retrofit*	9 1 5 9 0 0 1 9 8
GE DGP to 7xx Vertical Retrofit*	9 1 5 9 0 0 3 5 5
701/Simpro Retrofit Bezel*	9 1 5 9 0 0 1 9 7

	Vertical Retrofit (Siemens Q4 Tall SB with FT-1 Test Switch Cutout)*	9 1 5 9 0 0 1 4 0
	Vertical Retrofit (Square-D Power Logic 2000)*	9 1 5 9 0 0 2 7 5
Indoor Enclosure Brackets		
	7xx Indoor Enclosure Mounting Bracket + FT-1 Test Switch, Horizontal*	9 1 5 9 0 0 0 4 6
	7xx Indoor Enclosure Mounting Bracket, No FT-1 Cutout, Horizontal*	9 1 5 9 0 0 0 9 0
	7xx Indoor Enclosure Mounting Bracket + FT-1 Cutout Test Switch, Vertical*	9 1 5 9 0 0 0 6 5
	7xx Indoor Enclosure Mounting Bracket, No FT-1 Cutout, Vertical*	9 1 5 9 0 0 0 9 1
Outdoor Enclosure Kits		
	7xx Outdoor Enclosure Kit, Horizontal*	9 1 5 9 0 0 0 6 2
	7xx Outdoor Enclosure, No FT-1 Cutout, Horizontal*	9 1 5 9 0 0 0 9 2
	7xx Outdoor Enclosure Kit, Vertical*	9 1 5 9 0 0 0 6 6
	7xx Outdoor Enclosure, No FT-1 Cutout, Vertical*	9 1 5 9 0 0 0 9 3
Mounting Accessories		
	Mounting Brackets for 16" x 18" x 8" Enclosure*	9 1 5 9 0 0 2 9 7
	Mounting Gasket*	9 1 5 9 0 0 0 9 7
Current Transformers Clamp-On		
	Three 200:1 Clamp-On CTs, 0.6" Window, +-1% Accuracy*	9 1 5 9 0 0 2 0 9
	Three 1000:5 Clamp-On CTs, 2.0" Window, +-1% Accuracy*	9 1 5 9 0 0 2 1 0
Current Transformers Split-Core		
	Three 200:1 Split-Core CTs, 4.5" Window, +-3% Accuracy*	9 1 5 9 0 0 2 1 1

	Three 2000:5 Split-Core CTs, 6.0" Window, +-3% Accuracy*	9 1 5 9 0 0 2 1 2
	Three 3000:5 Split-Core CTs, 8.0" Window, +-3% Accuracy*	9 1 5 9 0 0 2 1 3
Projection Mounting Collar		
	Projection Mounting Collar, 45mm*	9 1 5 9 0 0 0 2 8
	Projection Mounting Collar, 90mm*	9 1 5 9 0 0 0 2 9
Blank Cover Plates		
	ABB-FT 21/22 (CO FT-2) Blank Cover Plate*	9 1 5 9 0 0 0 8 4
	GE S1 (IAC S1) Blank Cover Plate*	9 1 5 9 0 0 0 8 5
	GE M1 Blank Cover Plate*	9 1 5 9 0 0 1 4 2
	ABB-FT 31/32 (CO FT-3) Blank Cover Plate*	9 1 5 9 0 0 1 4 3
	ABB-FT 11 (CO FT-1) Blank Cover Plate*	9 1 5 9 0 0 1 4 4
	GE MDP/S2 Blank Cover Plate*	9 1 5 9 0 0 2 3 0
	241X / 7XX Blanker Plate*	9 1 5 9 0 0 3 8 7
Literature		
	Printed Instruction Manual ⁽¹⁾	P M 7 3 4 - 0 1

* Additional Cost

⁽¹⁾ The SEL-734 comes standard with a CD manual. One complimentary printed instruction manual is available upon request with each product purchased.

Optional Nameplate Information

SEL Assigned Nameplate

Customer Assigned Nameplate

A - Customer Text:
(30 Characters Max)

B - Barcode Information:
(17 Characters Max)

Valid Chars: ABCDEFGHIJKLMNOPQRSTUVWXYZ0123456789-\$/./+.

CUSTOMER NAME HERE



73400414924400000

SN: **2004149244**

CUSTOMER - SPECIFIED TEXT HERE



17 CHARAC BARCODE

SN: **2004149244**

Increments unless defined

Making Electric Power Safer, More Reliable, and More Economical®

SEL SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA
Phone: +1.509.332.1890 - Fax: +1.509.332.7990