

SEL-587Z

High-Impedance Differential Protection, Standard with 5 Outputs, 2 Inputs, Conventional Terminal Blocks

Part Number:

0	5	8	7	Z	0									2	X	X
---	---	---	---	---	---	--	--	--	--	--	--	--	--	---	---	---

Firmware

Standard	0
----------	---

Conformal Coat

None	X
Conformal Coated Circuit Boards*	2

Power Supply; Control Input Voltage⁽¹⁾

24 Vdc; 24 Vdc	1
48/125 Vdc or 125 Vac; 48 Vdc	2
48/125 Vdc or 125 Vac; 125 Vdc	3
125/250 Vdc or Vac; 250 Vdc	6

Energy-Clamping MOVs

1 MOV - 2500J, 2000V	1
2 MOVs - 5000J, 2000V*	2
4 MOVs - 8400J, 1500V*	3

Secondary Input Current

1 Amp Phase	1
5 Amp Phase	5

Mounting

Horizontal Rack Mount	H
Horizontal Panel Mount	3
Horizontal Projection Panel Mount*	5

Communications Port

EIA-232 Front and Rear Port	1
EIA-232 Front Port and EIA-485 Rear Port	2

Communications Protocol

Standard plus Modbus® RTU	2
---------------------------	---

Accessories

Literature	
SEL-587Z Printed English Instruction Manual ⁽²⁾	P M 5 8 7 Z - 0 1

* Additional Cost

⁽¹⁾ Control Input Voltage is jumper-selectable (24, 48, 125, 250 Vdc). Factory sets jumpers according to option selected.

⁽²⁾ The SEL-587Z comes standard with a CD manual. One complimentary printed instruction manual is available upon request with each product purchased.

High-impedance relay applications require a lockout (master) relay. If not already installed or available, the SEL-RS86 Lockout relay can be ordered separately.

Making Electric Power Safer, More Reliable, and More Economical®

SEL SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA
Phone: +1.509.332.1890 - Fax: +1.509.332.7990