

**SEL-2600**

Conformally coated RTD Module with 12 Inputs, Superior Noise Performance, V-Pin or ST® Fiber-Optic Port

Part Number:

2 6 0 0 0 X

**SELEct Power Supply Option**

120/240 Vac	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	A	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
125 Vdc	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	D	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>

**Firmware**

Standard	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	0	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
----------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	---	--------------------------	--------------------------	--------------------------	--------------------------

**Fiber-Optic Output Port (check Compatibility Guide below for selection)**

V-Pin connector with standard 3 m (9.8 feet) 200 µm fiber-optic cable <sup>(1)</sup> (SEL part number C805Z010VVX0003)	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	0	<input type="checkbox"/>
ST connector with standard 5 m (16.4 feet) Simplex 62.5 µm fiber-optic cable <sup>(1)</sup> (SEL part number C807Z010SSX0005)	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	1	<input type="checkbox"/>

<sup>(1)</sup> Additional Cost for non-standard cable length; contact SEL representative.

Note: The SEL-2600 comes standard with a CD manual. A printed instruction manual is available upon request.

For an SEL-2600 installation requiring other than the standard fiber-optic cable length, order the following fiber-optic cable part numbers:

**SEL-2600A/D00X (V-Pin)**

- C805Z010VVXxxxx - standard-duty, low-cost, zip-cord 200 µm multimode fiber-optic cable (cannot be exposed to direct sunlight).  
Please specify the length xxxx in meters (maximum 500 m or 1640 feet) e.g., 0100 for 100 meters.

**SEL-2600A/D01X (ST)**

- C807Z010SSX0001 - 1 m (3.3 feet) Simplex 62.5 µm multimode fiber-optic cable ST/ST.
  - C807Z010SSX0015 - 15 m (49.2 feet) Simplex 62.5 µm multimode fiber-optic cable ST/ST.
- Please specify the length XXXX in meters (maximum 1000 m or 3280 feet) e.g., 0100 for 100 meters

Compatibility Guide	
SEL-2600 connected to Fiber Optic Port on the relay	SEL-2600 connected to EIA-232 <sup>(3)</sup> port or EIA-485 <sup>(4)</sup> port on the relay
<p><u>V-Pin connector options only</u></p> <ul style="list-style-type: none"> <li>• SEL-701-Motor Protection Relay</li> <li>• SEL-701-1 Monitor</li> </ul> <p><u>ST connector options only</u></p> <ul style="list-style-type: none"> <li>• SEL-749M Motor Protection Relay</li> <li>• SEL-710 Motor Protection Relay</li> <li>• SEL-751 Feeder Protection Relay</li> <li>• SEL-751A Feeder Protection Relay</li> <li>• SEL-700G Generator Protection Relay<sup>(2)</sup></li> <li>• SEL-787 Transformer Protection Relay</li> <li>• SEL-710-5 Motor Protection Relay</li> <li>• SEL-787-3,-4 Transformer Protection Relay</li> <li>• SEL-2411 Programmable Automation Controller</li> <li>• SEL-2414 Transformer Monitor</li> </ul>	<p><u>Both V-Pin and ST connector options</u></p> <ul style="list-style-type: none"> <li>• SEL-387A Current Differential and Overcurrent Relay</li> <li>• SEL-352-2,-3 Breaker Failure Relay</li> <li>• SEL-387-5,-6 Current Differential Overcurrent Relay</li> <li>• SEL-300G Multifunction Generator Relay</li> <li>• SEL-421 Protection, Automation, and Control System</li> <li>• SEL-451 Protection, Automation, and Control System</li> <li>• SEL-411L Advanced Line Differential Protection, Automation, and Control System</li> <li>• SEL-487B Bus Differential and Breaker Failure Relay</li> <li>• SEL-487E Transformer Protection Relay</li> <li>• SEL-487V Capacitor Protection and Control System</li> <li>• SEL-3530 Real-Time Automation Controller (RTAC), SEL-2032 or SEL-2030 Communications Processor</li> </ul>

<sup>(2)</sup> SEL-700G also supports SEL-2600 RTD module on EIA -232 port using the SEL-2812M or SEL-2814M for ST connectors and SEL-2800M Fiber-Optic Transceiver for V-pin connectors ; on the EIA 485 port using SEL-2820 V-Pin transceiver for V-pin connectors and SEL-2824 Fiber-Optic Transceivers for ST connectors.

<sup>(3)</sup> Requires SEL-2812M or SEL-2814M for ST connectors and SEL-2800M Fiber-Optic Transceiver for V-pin connectors

<sup>(4)</sup> Requires SEL-2820 V-pin Transceiver for V-pin connectors and SEL-2824 Fiber-Optic Transceivers or SEL-9220 Fiber-Optic Adapter<sup>(5)</sup> for ST connectors

<sup>(5)</sup> SEL-9220 Fiber-Optic Adapter can be used with SEL-3xx series relays only

ST is a registered trademark of AT&T.

*Making Electric Power Safer, More Reliable, and More Economical®*